



Catalog No. 5337-T6

Description: 2 INCH LIQ.TIGHT CONN UL TYPE 6

UPC No 786209917997

Home > Cable Protection Systems > T&B Liquidtight Fittings > Liquid tight connectors

2 Inch Liquidtight Fitting, Metal Conduit Connector, Straight, Insulated, Safe-edge Ground Cone, In K.O. Applications Use Sealing Ring #5267, Electro Zinc Plated to Chrome Coated, UL Listed Type 6, 5 Pieces

Descriptors

Category	Liquid tight connectors
----------	-------------------------

Specifications

Finish	Chromate
--------	----------

Classifications

Brand Name	T&B Liquidtight Fittings
Standard	UL Listed

Dimensions

Size	2 Inch
------	--------

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Steel
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UL	Y

—
by ABB