

Catalog No. 540-41131

Description: CBL TIE 40LB 8IN GRAY NYL

UPC No 786210068169

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Gray Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 208mm (8.19 Inches), Width of 3.6mm (0.14 Inches), Thickness of 1.04mm (0.04 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds)



Representative Image

Descriptors

Category	Cable ties
Application	For Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications

Specifications

Material	Nylon/Polyamide 6.6
Color	Gray
Lock Mechanism	Stainless Steel Barb
Tensile Strength	40 pounds , 180 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL/EN/CSA62275 Type 2/21, compliant for plenum AH-2 UL/EN/CSA62275 Type 2/21, compliant for plenum AH-2

Dimensions

Width	0.142 in , 3.6 mm
Length	8.19 in , 208 mm
Thickness	0.041 in , 1.04 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Band width	3.6 mm
Length belt/tape/tie	208 mm

ETIM	EC000046 Cable tie
Length belt/tape/tie	8.19 inch
Tie thickness	1.04 mm
Tie thickness	0.041 inch
Min. holding force	180 N
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
Halogen free	Y
Colour	Grey
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N