



Representative Image

Catalog No. 540-41132

Description: CBL TIE 40LB 11IN GRAY NYL

UPC No 786210066387

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Gray Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 284.4mm (11.19 Inches), Width of 3.71mm (0.146 Inches), Thickness of 1.31mm (0.052 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds)

Descriptors

Category	Cable ties
Application	For Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications

Specifications

Material	Nylon/Polyamide 6.6
Color	Gray
Lock Mechanism	Stainless Steel Barb
Tensile Strength	40 pounds , 180 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum

Dimensions

Width	0.146 in , 3.71 mm
Length	11.08 in , 284.4 mm
Thickness	0.05 in , 1.31 mm

ETIM	EC000046 Cable tie
Band width	3.71 mm
Length belt/tape/tie	284.4 mm
Length belt/tape/tie	11.19 inch
Tie thickness	1.31 mm
Tie thickness	0.05 inch
Min. holding force	180 N
Model	Internal tothing
Band closure	Steel nose

by ABB

ETIM	EC000046 Cable tie
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
Halogen free	Y
Colour	Grey
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N