



Representative Image

Catalog No. 1SNA645547R0200**Description:** OBRIC0100-5-12VDC Optocoupler R600 A1-A2=5-12VDC,4.5-58VDC/1 mA-100 mA,Transistor**UPC No** 4013614508462**Home > Controls & Protective Relays > Interface Relays & Optocouplers****Descriptors**

Category	Interface Relays & Optocouplers
----------	---------------------------------

Specifications

Function	Boxed optocoupler R600
Rated Control Supply Voltage	5 ... 12 V DC
Output Signal	4.5 ... 58VDC / 1 mA ... 100 mA
Terminal Type	Spring Terminals
Output	solid-state output
Contact material	Transistor
Product Main Type	R600
RoHS Status	Following EU Directive 2011/65/EU
Object Classification Code	K

Classifications

ETIM 4	EC001504 - Optocoupler
ETIM 5.0	EC001504 - Optocoupler
ETIM 6.0	EC001504 - Optocoupler
ETIM 7	EC001504 - Optocoupler
eClass	7.0 27371604

Dimensions

Product Net Width	6 mm
Product Net Height	67.5 mm
Product Net Depth / Length	75 mm
Product Net Weight	0.02kg

Package Information

Package Level 1 Units	10 piece
Package Level 1 Width	73 mm

by ABB

Package Information

Package Level 1 Height	71 mm
Package Level 1 Depth / Length	80 mm
Package Level 1 Gross Weight	0.23 kg
Package Level 1 EAN	3472596455477

Ordering

Minimum Order Quantity	10
Customs Tariff Number	85369095
ECCN	N
ECN	N
ABB MDF Code	3DL - Relays (LV / Control + Protection)
ABB Business Unit	ELSP - Smart Power