



Representative Image

**Alternate Catalog No. SU204M-K40**  
**Catalog No. 2CDS274337R0557**

**Description:** UL489 MCB 4P K 40A 240

**UPC No 4016779930703**

**Home > Circuit Breakers > Miniature Circuit Breakers > UL 489 Branch Circuit MCBs**

SU204M-K40 Miniature Circuit Breaker K-Char., 10kA, 40A, 4P UL489

**Descriptors**

|          |                            |
|----------|----------------------------|
| Category | UL 489 Branch Circuit MCBs |
|----------|----------------------------|

**Specifications**

|                                                |                                                      |
|------------------------------------------------|------------------------------------------------------|
| Number of Poles                                | 4                                                    |
| Tripping Characteristic                        | K                                                    |
| Rated Current                                  | 40 A                                                 |
| Standards                                      | CSA 22.2 No. 5<br>IEC/EN 60947-2<br>UL 489           |
| Product Main Type                              | SU200M                                               |
| Rated Voltage (V)                              | (240 V AC)<br>(96 V DC)                              |
| Interrupting Rating acc. to UL489              | (240 V AC) 10 kA<br>(96 V DC) 10 kA                  |
| Rated Ultimate Short-Circuit Breaking Capacity | (400 V AC) 15 kA                                     |
| Power Loss                                     | 18 W<br>at Rated Operating Conditions per Pole 4,5 W |