

**Alternate Catalog No. SU202MR-K0.3**  
**Catalog No. 2CDS272347R0117**

**Description: MCB SU200MR RTT 2P K 0.3A BCP**

**UPC No 4016779957199**

**Home > Circuit Breakers > Miniature Circuit Breakers > UL 489 Branch Circuit MCBs**

SU202MR-K0.3 MCB K-Char., 10kA, 0.3A, 2P, RTT UL 489, Ring Cable Lug



**Descriptors**

Category	UL 489 Branch Circuit MCBs
----------	----------------------------

**Specifications**

Number of Poles	2
Tripping Characteristic	K
Rated Current	0.30 A
Product Main Type	SU200MR
Rated Voltage (V)	(480Y / 277 V AC) (96 V DC)
Interrupting Rating acc. to UL489	(480Y / 277 V AC) 10 kA (96 V DC) 10 kA
Power Loss	at Rated Operating Conditions per Pole 1.7 W