



Representative Image

Catalog No. 9T21B1005G02

Description: 1A,7.5kVA,240x480-120/240,115C,3R,QMS

UPC No 783173003954

Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

ABB's QMS single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T7

Specifications

Phase	1
PriVoltage	240x480
SecVoltage	120/240
KVA	7.5 KVA
Coil Material	AL
TempRise	115.0 °C
ElecShield	N
Sub Type	Standard
Frequency	60 Hz
FrameSize	16600
Net Weight	147
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
KFactor	K1
Enclosure Type	NEMA 3R
Net Weight	147
Sound	Std
GSA Compliance	No

Classifications

UL	Yes
cUL	Yes
CE	No

Dimensions

Width	10.6 in
Depth	11.0 in
Height	17.1 in