



Representative Image

Catalog No. 7341

Description: 3/8IN 45D LT INSUL CONN PG11 STL

UPC No 786210073415

Home > Cable Protection Systems > T&B Liquidtight Fittings > Liquid tight connectors

3/8 Inch 45 Degree Steel Insulated Liquidtight Connector With PG Thread and Chromate Finish, Thread Size 11

Descriptors

Category	Liquid tight connectors
Special Features	CSA Certified Dusttight and Watertight. UL Listed Liquidtight.
Application	Nylon Insulated 45D Angle Fittings

Specifications

Material	Nylon Insulated
----------	-----------------

Classifications

Brand Name	T&B Liquidtight Fittings
Standard	CSA, UL E23018

Dimensions

Size	3/8 Inch
------	----------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/8 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	Other
Thread connection size	PG11

by ABB

ETIM	EC001180 Screw connection for protective metallic hose
One-piece	N
Material housing	Steel
Thread length	14 mm
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y