



Representative Image

Catalog No. 9T21C3326G02

Description: "1C,5kVA,480-120/240,115C,N3R,60Hz,QMS"

UPC No 783173012079

Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

ABB's QMS single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descriptors

Category

Single-Phase: .050kVA-3kVA and 5kVA-25kVA

Specifications

Phase	1
PriVoltage	480
SecVoltage	120/240
KVA	5.0 KVA
Coil Material	CU
TempRise	115.0 °C
ElecShield	N
Sub Type	Standard
Frequency	60 Hz
FrameSize	16350
Net Weight	111
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
KFactor	K1
Enclosure Type	NEMA 3R
Net Weight	111
GSA Compliance	No

Classifications

UL	Yes
cUL	Yes
CE	No

Dimensions

Width	10.6 in
Depth	11.0 in

Dimensions

Height	14.5 in
--------	---------