



Representative Image

**Alternate Catalog No. XT2NU3020AFF000XXX**  
**Catalog No. 1SDA074734R1**

**Description:** XT2N 125 TMF 20-400 3P F F UL/CSA

**UPC No** 8015644787110

**Home > Circuit Breakers > Molded Case Circuit Breakers > SACE Tmax XT**

C.BREAKER TMAX XT2N 125 UL/CSA FIXED THREE-POLE WITH FRONT TERMINALS AND THERMOMAGNETIC RELEASE TMF R 20-400 A

**Descriptors**

|          |              |
|----------|--------------|
| Category | SACE Tmax XT |
|----------|--------------|

**Specifications**

|                       |                                   |
|-----------------------|-----------------------------------|
| Trip Unit             | TMF                               |
| Product Main Type     | SACE Tmax XT                      |
| Frame size            | XT2                               |
| Extended Product Type | XT2N 125 TMF 20-400 3p F F UL/CSA |
| Standards             | UL                                |
| Rated Voltage (V)     | 600 V                             |
| Rated Current         | 20 A                              |
| Interruption Rating   | N (25kA @480VAC)                  |
| Number of Poles       | 3                                 |

**Approvals**

|               |    |
|---------------|----|
| Certification | UL |
|---------------|----|