

Alternate Catalog No. S202MUC-C20
Catalog No. 2CDS272061R0204

Description: MCB S200MUC 2P C 20A AC/DC

UPC No 4013614433023

Home > Circuit Breakers > Miniature Circuit Breakers > Supplementary Protectors

Representative Image

Descriptors

Category	Supplementary Protectors
----------	--------------------------

Specifications

Number of Poles	2
Tripping Characteristic	C
Rated Current	20 A
Product Main Type	S200MUC
Rated Voltage (V)	(500 V DC) (480Y / 277 V AC)
Interrupting Rating acc. to UL1077	(500 V DC) 10 kA (480Y / 277 V AC) 6 kA
Rated Short-Circuit Capacity	(253 V AC) 10 kA (400 V AC) 10 kA (440 V DC) 10 kA
Rated Ultimate Short-Circuit Breaking Capacity	(220 V DC) 25 kA (440 V AC) 10 kA (440 V DC) 10 kA
Power Loss	4.5 W at Rated Operating Conditions per Pole 2.26 W