



Representative Image

Catalog No. 9T58K2979

Description: 1C,0.75kVA,416>380-115/230,100C,5/6Hz,IP

UPC No 783173154595

Home > Transformers > Dry Type, Encapsulated Core & Coil > Control Power

ABB's General purpose encapsulated open core, and coil transformer (also known as Type IP Control Power transformers) are ideally suited for industrial and light-duty loads, HVAC applications, signal and alarm systems, industrial control panels, lighting, and circuit isolation. The optional fuse block adapter kits enable input and output flexibility. Type IP Control Power transformers are an economical alternative to high in-rush/machine tool transformers.

Descriptors

Category	Control Power
GO Schedule	TQ

Specifications

Phase	1
PriVoltage	380/400/416
SecVoltage	115/230
KVA	0.75 KVA
Coil Material	CU
TempRise	100.0 °C
ElecShield	N
Sub Type	Control Terminal Block
Frequency	50 Hz
FrameSize	12300
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
KFactor	K1
Enclosure Type	None
PriRatingType	8
SecRatingType	8
Outline	303B947AAP12300
TransType	IP

Classifications

UL	Yes
cUL	Yes