



Representative Image

Catalog No. 9T33C2670

Description: 1C,15KVA,240X480-120/240,150C,N2,DOE/NRC

UPC No 783173365649

Home > Transformers > Dry Type Vented > General Purpose

ABB's 9T33 Single phase low-voltage dry type transformers are for balanced 3-wire 120/240 V secondary voltage systems having both NRCan (C802.2) and DOE (10 CFR 431, Subpart K) energy efficiency certification and compliance. UL and cUL listed to UL 1561 and CSA C22.2 No.47. Qualified to the seismic requirements of IEEE-693-2005 and the IBC-2021 and CBC 2022. The 9T33 transformers are also UL Energy Verified.

Descriptors

Category	General Purpose
----------	-----------------

Specifications

TransType	QL
Phase	1
PriVoltage	240x480
SecVoltage	120/240
KVA	15.0 KVA
Coil Material	CU
TempRise	150.0 °C
Sub Type	VENTED
Frequency	60 Hz
TempClass	220.0 °C
AmbTemp	40 °C
EnergyEfficiency	DOE/NRC
KFactor	K1
Enclosure Type	NEMA 2
Taps (FCBN,FCAN	-4,+2, 2.5%

Classifications

UL	Yes
cUL	Yes