



Representative Image

Catalog No. DBRE131610000/A200

Description: 100A,ILK,3P4W,MG,120/208V,XP,2@A

UPC No 708917305576

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Interlocked Receptacle, Explosion Proof, 100 Amp, 3 Pole 4 Wire, 120/208V, 60Hz, 2 inch at A

Descriptors

| | |
|------------------|---|
| Category | Electrical sleeves |
| Special Features | Explosion-proof waterproof circuit breaker interlocked receptacle O-ring sealed along with optional control contacts fully UL listed. |
| Application | For use with watertight plugs and inlets where portable equipment is on stand by and plugs are not in use. |

Specifications

| | |
|-----------------|---------------|
| Number Of Poles | 3 |
| Number Of Wires | 4 |
| Amperage Rating | 100 Amps |
| Voltage Rating | 208 V |
| Material | Cast Aluminum |

Classifications

| | |
|------------|--------------|
| Brand Name | Russellstoll |
|------------|--------------|

ETIM Classification

| | |
|-----------------|--|
| ETIM | EC001322 Round socket/plug for high currents |
| Amperage | 100 A |
| Number of poles | 3 |

by ABB