



**Catalog No. A252G**

**Description: NON-INS FEM-250 FLAG DISC, 22-18 LE**

**UPC No 786210878980**

**Home > Connectivity & Grounding > Sta-Kon > Wire terminal disconnect**

Non-Insulated 90 Degree Flag Female Disconnect, Length .58 Inches, Width .61 Inches, Tab Size .250x.032, Wire Range #22-#18 AWG, Copper, Tin Plated, 500 Pack

**Descriptors**

Category	Wire terminal disconnect
Special Features	Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.

**Specifications**

Material	Brass
Finish	Tin Plated
Color	Metallic
Insulation	None

**Classifications**

Brand Name	Sta-Kon
Standard	UL E66716 UL E66716

**Compliance and Certifications**

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Not isolated
Material	Copper
AWG-range	22-18