



Catalog No. A85M

Description: NON-INS RING TERM 22-16 NO6 MYLAR

UPC No 786210859323

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Non-Insulated Ring Terminal, Length .72 Inches, Width .25 Inches, Bolt Hole #6, Wire Range #22-16 AWG, Copper, Tin Plated, On Mylar Tape, 1,000 Pack

Descriptors

Category	Electrical terminals
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.
Application	Wiring terminations for wiring harness, panelboard, telecommunications, and automotive.

Specifications

Voltage Rating	600 V
Material	Copper
Color	Metallic

Classifications

Brand Name	Sta-Kon
Standard	UL E9809 UL E9809

Dimensions

Wire Size	22-16 AWG
-----------	-----------

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	Y
AWG-range	22-16
Material	Copper
Surface protection	Tinned
Stud size (imperial)	6