



Representative Image

Catalog No. AA2

Description: NON-INS BTT SPLCE 22-16AWG LEN .63

UPC No 786210808888

Home > Connectivity & Grounding > Sta-Kon > Wire or cable compression splice

Non-Insulated Butt Splice, Length 0.63 Inch, Width 0.12 Inches, Wire Range 22-16 AWG, Copper, Tin Plated, 1,000 Pack

Descriptors	
Category	Wire or cable compression splice
Specifications	
Conductor Range	22-16 AWG
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Voltage Rating	600 V
Insulation	None
Temperature Rating	150 C
Classifications	
Brand Name	Sta-Kon
Standard	UL E9809 UL E9809
Compliance and Certifications	
RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant