



**Catalog No. B220M**

**Description: NONINS LKG FORK TRM 18-14 NO6 MYLAR**

**UPC No 786210860183**

**Home > Connectivity & Grounding > Sta-Kon > Electrical terminals**

Non-Insulated Locking Fork Terminal, Length .75 Inches, Width .25 Inches, Bolt Hole #6, Wire Range #18-#14 AWG, Copper, Tin Plated, On Mylar Tape, 1,000 Pack

**Descriptors**

Category	Electrical terminals
Special Features	Locking fork terminals have a specially designed tongue that lets them go on like a fork and stay on like a ring.

**Specifications**

Voltage Rating	600 V
Material	Copper
Color	Metallic

**Classifications**

Brand Name	Sta-Kon
Standard	UL E9809 UL E9809

**Dimensions**

Wire Size	18-14 AWG
-----------	-----------

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Fork shape
Insulation	None
Reel packaging	Y
AWG-range	18-14
Material	Copper
Surface protection	Tinned
Stud size (imperial)	6