



Catalog No. B225M

Description: NONINS LKG FRK TRM 18-14 NO10 MYLAR

UPC No 786210860206

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Non-Insulated Locking Fork Terminal, Length .75 Inches, Width .29 Inches, Bolt Hole #10, Wire Range #18-#14 AWG, Copper, Tin Plated, On Mylar Tape, 1,000 Pack

Descriptors

Category	Electrical terminals
----------	----------------------

Specifications

Material	Copper
----------	--------

Classifications

Brand Name	Sta-Kon
Standard	UL E9809 UL E9809

Dimensions

Wire Size	18-14 AWG
-----------	-----------

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Fork shape
Insulation	None
Reel packaging	Y
AWG-range	18-14
Material	Copper
Surface protection	Tinned
Stud size (imperial)	10