



Representative Image

## Catalog No. B87M

**Description:** NON-INS RING TERM 18-14 No10 BELT

**UPC No** 786210859903

**Home > Connectivity & Grounding > Sta-Kon > Electrical terminals**

Non-Insulated Ring Terminal, Length .75 Inches, Width .31 Inches, Bolt Hole #10, Wire Range #18-#14 AWG, Copper, Tin Plated, On Mylar Tape, 1,000 Pack

### Descriptors

Category	Electrical terminals
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.
Application	Wiring terminations for wiring harness, panelboard, telecommunications, and automotive.

### Specifications

Voltage Rating	600 V
Material	Copper
Color	Metallic

### Classifications

Brand Name	Sta-Kon
Standard	UL E9809 UL E9809

### Dimensions

Wire Size	18-14 AWG
-----------	-----------

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	Y
AWG-range	18-14
Material	Copper
Surface protection	Tinned
Stud size (imperial)	10