



Representative Image

Catalog No. C10-PS-D

Description: NON-INS PRL SPLICE, 12-10, CMA 5,18

UPC No 786210936277

Home > Connectivity & Grounding > Sta-Kon > Wire or cable compression splice

Non-Insulated Parallel Splice, Length 0.30 Inch, Outer Diameter 0.22 Inch, Inner Diameter 0.17 Inches, Wire Range #12-#10 AWG 5,180 kcmil-13,100 kcmil, Copper, Tin Plated

Descriptors

Category	Wire or cable compression splice
Special Features	Resistant to corrosion and preserve the electrical integrity of the wires in single or multiple strands. Feature an intelligent constructable part number for quick identification of the wire range.

Specifications

Material	Copper
Finish	Tin Plated
Color	Metallic
Voltage Rating	600 V

Classifications

Brand Name	Sta-Kon
Standard	UL E9809 UL E9809

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001059 Crimp splices for copper conductor
Material	Copper
Surface protection	Tinned
Insulation	None