



Representative Image

Catalog No. CH803AMV

Description: A3 SINGLE LOCK SYS 1XPG11-3/8

UPC No 786209986955

Home > Connectivity & Grounding > Pos-E-Kon > Terminal block covers

Coupler Hood, Inline, Top Entry, A3/A4, Single Lock Lever System, Metal Levers. Straight. 3/8 inch.

Descriptors

Category	Terminal block covers
----------	-----------------------

Specifications

Material	Die-Cast Aluminum Alloy
Finish	Epoxy Powder Coated
Temperature Rating	-40 to +257 F

Classifications

Brand Name	Pos-E-Kon
Standard	UL E215386

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000437 Housing for rectangular connectors
Width	22.86 mm
Height	60.5028 mm
Type of housing	Coupling housing
Material housing	Aluminium
Coating housing	Powder coating
Position cable feed	Sideways
With cable screw gland	N
With hinged lid	N
Inflammability class of insulation material acc. with UL94	V0
Operation temperature	-40 - +125 °C
Degree of protection (IP), mounted	Other

by ABB