



Representative Image

Catalog No. CH816AMV

Description: SLG LEVR LKG CPL HOOD TOP ENTR 1X.5

UPC No 786209987532

Home > Connectivity & Grounding > Pos-E-Kon > Terminal block covers

Single lever locking inline coupler hood with top entry, 16 contacts, NPT entry - 1 Inch x 1/2 Inch

Descriptors

Category	Terminal block covers
Application	For inline, portable or special service connections

Specifications

Material	Die-Cast Aluminum Alloy
Finish	Epoxy Powder Coated
Temperature Rating	-40 to +257 F

Classifications

Brand Name	Pos-E-Kon
Standard	UL E215386

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000437 Housing for rectangular connectors
Width	29.4894 mm
Height	56.9976 mm
Type of housing	Coupling housing
Material housing	Aluminium
Coating housing	Powder coating
Position cable feed	Sideways
With cable screw gland	N
With hinged lid	N
Inflammability class of insulation material acc. with UL94	V0
Operation temperature	-40 - +125 °C



ETIM	EC000437 Housing for rectangular connectors
Degree of protection (IP), mounted	Other