



**Catalog No. CMP500-6-A**

**Description:** SHRINK-KON-1,22M

**UPC No** 5414363102861

**Home > Connectivity & Grounding > Shrink-Kon > Heat shrinkable tube**

Heat Shrink Tubing, 12.7mm, Blue, 1.22m Cut Length, 25 per box

**Descriptors**

Category	Heat shrinkable tube
----------	----------------------

**Specifications**

Shrink Ratio	2:1
Color	Blue

**Classifications**

Brand Name	Shrink-Kon
------------	------------

**Dimensions**

Thickness	Thin
Length	492.1 ft , 150 m

**Compliance and Certifications**

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

**ETIM**

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	12.7 mm
Inner diameter before heat-shrink	0.5 inch
Inner diameter after heat-shrink	6.4 mm
Inner diameter after heat-shrink	0.25 inch
Nominal diameter inch	1/2 inch



ETIM	EC000217 Shrink tubing
Wall thickness after shrinking	0.6 mm
Wall thickness after shrinking	0.02 inch
Length	1.22 m
Length	4 ft
Operation temperature	-55-+135 °C
Operation temperature	-67-+275 °F
Colour	Blue
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y