



Representative Image

Catalog No. CSS-135

Description: CABLE SUPPORT 13.5 INCH

UPC No 786210700663

Home > Wire & Cable Management > Deltec > Cable ties

Deltec Cable Tie with Double-Locking Head, Black Acetal for Temperatures up to 105 Degrees Celsius (221 F), Weather and Ultraviolet Resistant, Length of 342.90mm (13.5 Inches), Width of 12.7mm (0.5 Inch, Thickness of 1.52mm (0.06 Inch), Tensile Strength Rating of 1112 Newtons (250 Pounds)

Descriptors

Category	Cable ties
Special Features	Perfect for coaxial, fiber optic and all other communication and electrical conducting cables.
Application	Ideal solution for bundling in harsh outdoor environments.

Specifications

Material	Weather Resistant Acetal
Color	Black
Lock Mechanism	Double Locking Head
Tensile Strength	250 pounds , 1112 newtons

Classifications

Brand Name	Deltec
------------	--------

Dimensions

Width	0.5 in , 12.7 mm
Length	13.5 in , 342.9 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 233 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Band width	12.7 mm
Length belt/tape/tie	342.9 mm
Length belt/tape/tie	13.5 inch
Tie thickness	1.52 mm

by ABB

ETIM	EC000046 Cable tie
Tie thickness	0.06 inch
Min. holding force	1112 N
Operation temperature	-40-+105 °C
Operation temperature	-40-+221 °F
Model	Internal tothing
Band closure	Double lock head
Material	Plastic
Material quality	Other
Surface protection	Untreated
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N