



Catalog No. CSS-360

Description: MODULAR STACKABLE CBL SPACER BLK

UPC No 786210568041

Home > Wire & Cable Management > Deltec > Cable ties

Deltec Modular Stackable Cable Spacer, Black Polypropylene for Temperatures up to 105 Degrees Celsius (221 F), Weather and Ultraviolet Resistant, Height of 12.7mm (0.50 Inch), 100 Pack

Descriptors

Category	Cable ties
Special Features	Perfect for coaxial, fiber optic and all other communication and electrical conducting cables.
Application	Ideal solution for bundling in harsh outdoor environments.

Specifications

Material	Weather-Resistant Polypropylene
Color	Black
Tensile Strength	250 pounds , 1112 newtons

Classifications

Brand Name	Deltec
------------	--------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

Technical Data

ETIM	EC000046 Cable tie
Operation temperature	-40-+105 °C
Operation temperature	-40-+221 °F
Material	Plastic
Material quality	Polypropylene
Surface protection	Untreated
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None

by ABB

ETIM	EC000046 Cable tie
Solvable fastener	N
MIL approval	N