

## Catalog No. CSS-LH



Representative Image

**Description: HEADS,CABLE SUPPORT**

**UPC No 786210701721**

**Home > Wire & Cable Management > Deltec > Cable ties**

Deltec Cable Tie Locking Head Only, Black Acetal for Temperatures up to 105 Degrees Celsius (221 F), Length of 21.59mm (0.85 Inches), Width of 19.05mm (0.75 Inch), Height of 12.57mm (0.495 Inch), Weather and Ultraviolet Resistant, Bulk Pack

### Descriptors

Category	Cable ties
Special Features	Perfect for coaxial, fiber optic and all other communication and electrical conducting cables.
Application	Ideal solution for bundling in harsh outdoor environments.

### Specifications

Material	Weather Resistant Acetal
Color	Black
Lock Mechanism	Double Locking Head
Tensile Strength	250 pounds , 1112 newtons

### Classifications

Brand Name	Deltec
------------	--------

### Dimensions

Width	0.75 in , 19.05 mm
Length	0.85 in , 21.59 mm

### Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Band width	19.05 mm
Length belt/tape/tie	21.59 mm
Length belt/tape/tie	0.85 inch
Operation temperature	-40-+105 °C

by ABB

ETIM	EC000046 Cable tie
Operation temperature	-40-+221 °F
Model	Internal toothng
Band closure	Double lock head
Material	Plastic
Material quality	Polyoxymethylene (POM)
Surface protection	Untreated
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N