



Representative Image

Catalog No. DBRE6207060K0

Description: 60A,ILK,2P3W,MG,207,250V,0K0,XP,CC

UPC No 708917314363

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Interlocked Receptacle, Explosion Proof with Control Contacts, 60 Amp, 2 Pole 3 Wire, 250V, 60Hz

Descriptors

Category	Electrical sleeves
Special Features	Explosion-proof waterproof circuit breaker interlocked receptacle O-ring sealed along with optional control contacts fully UL listed.
Application	For use with watertight plugs and inlets where portable equipment is on stand by and plugs are not in use.

Specifications

Number Of Poles	2
Number Of Wires	3
Amperage Rating	60 Amps
Voltage Rating	250 V
Material	Cast Aluminum

Classifications

Brand Name	Russellstoll
------------	--------------

ETIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	60 A
Number of poles	2