



Representative Image

## Catalog No. DBRE6304060K0

**Description:** 60A,ILK,3P4W,MG,304,0K0,277/480V,XP

**UPC No** 708917307020

**Home > Connectivity & Grounding > Russellstoll > Electrical sleeves**

MaxGard Interlocked Receptacle, Explosion Proof with Control Contacts, 60 Amp, 3 Pole 4 Wire, 277/480V, 60Hz

### Descriptors

|                  |                                                                                                                                       |
|------------------|---------------------------------------------------------------------------------------------------------------------------------------|
| Category         | Electrical sleeves                                                                                                                    |
| Special Features | Explosion-proof waterproof circuit breaker interlocked receptacle O-ring sealed along with optional control contacts fully UL listed. |
| Application      | For use with watertight plugs and inlets where portable equipment is on stand by and plugs are not in use.                            |

### Specifications

|                 |               |
|-----------------|---------------|
| Number Of Poles | 3             |
| Number Of Wires | 4             |
| Amperage Rating | 60 Amps       |
| Voltage Rating  | 480 V         |
| Material        | Cast Aluminum |

### Classifications

|            |              |
|------------|--------------|
| Brand Name | Russellstoll |
|------------|--------------|

### ETIM Classification

|                 |                                              |
|-----------------|----------------------------------------------|
| ETIM            | EC001322 Round socket/plug for high currents |
| Amperage        | 60 A                                         |
| Number of poles | 3                                            |