



Representative Image

## Catalog No. DBRF111610000

**Description:** 100A,ILK,2P3W,MG,116,120V,FC

**UPC No** 708917274766

**Home > Connectivity & Grounding > Russellstoll > Electrical sleeves**

MaxGard Interlocked Flap Cap Receptacle with Circuit Breaker, 100 Amp, 2 Pole 3 Wire, 120V, 60Hz

### Descriptors

|                  |                                                                                                                                                                  |
|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Category         | Electrical sleeves                                                                                                                                               |
| Special Features | Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight"). |
| Application      | For use with watertight plugs and inlets where portable equipment is on stand by and plugs are not in use.                                                       |

### Specifications

|                 |               |
|-----------------|---------------|
| Number Of Poles | 2             |
| Number Of Wires | 3             |
| Amperage Rating | 100 Amps      |
| Voltage Rating  | 120 V         |
| Material        | Cast Aluminum |

### Classifications

|            |              |
|------------|--------------|
| Brand Name | Russellstoll |
|------------|--------------|

### ETIM Classification

|                 |                                              |
|-----------------|----------------------------------------------|
| ETIM            | EC001322 Round socket/plug for high currents |
| Amperage        | 100 A                                        |
| Number of poles | 2                                            |