



Representative Image

## Catalog No. DBRF130410000

**Description: 100A,ILK,3P4W,MG,304,277/480,FC**

**UPC No 708917140962**

**Home > Connectivity & Grounding > Russellstoll > Electrical sleeves**

MaxGard Interlocked Flap Cap Receptacle with Circuit Breaker, 100 Amp, 3 Pole 4 Wire, 277/480V, 60Hz

### Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	For use with watertight plugs and inlets where portable equipment is on stand by and plugs are not in use.

### Specifications

Number Of Poles	3
Number Of Wires	4
Amperage Rating	100 Amps
Material	Cast Aluminum

### Classifications

Brand Name	Russellstoll
------------	--------------

### FTIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	100 A
Number of poles	3

by ABB