



Representative Image

Catalog No. DBRF151610000

Description: 100A,ILK,4P5W,MG,516,3PY208V,FC

UPC No 708917403449

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Interlocked Flap Cap Receptacle with Circuit Breaker, 100 Amp, 4 Pole 5 Wire, 30Y 120/208V, 60Hz

Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	For use with watertight plugs and inlets where portable equipment is on stand by and plugs are not in use.

Specifications

Number Of Poles	4
Number Of Wires	5
Amperage Rating	100 Amps
Voltage Rating	208 V
Material	Cast Aluminum

Classifications

Brand Name	Russellstoll
------------	--------------

ETIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	100 A
Number of poles	4