



Representative Image

Catalog No. DBRF252120000

Description: 200A,ILK,4P5W,MG,521,3PY440V,FC

UPC No 708917192657

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

Maxgard Interlocked Receptacle with Circuit Breaker, 200 Amp, 4 Pole 5 Wire, 30y 250/440Vv, 60Hz

Descriptors

Category	Electrical sleeves
----------	--------------------

Specifications

Number Of Poles	4
Number Of Wires	5
Amperage Rating	200 Amps
Voltage Rating	250/440 V

Classifications

Brand Name	Russellstoll
Standard	UL e57324 UL e57324

ETIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	200 A
Number of poles	4