



Representative Image

Catalog No. DBRF341403000

Description: 30A,ILK W/ CB,3P4W,MG,414,3P600V,FC

UPC No 708917178996

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

Maxgard Interlocked Receptacle with Circuit Breaker, 30 Amp, 3 Pole 4 Wire, 30 600V, 60Hz

Descriptors

Category	Electrical sleeves
----------	--------------------

Specifications

Number Of Poles	3
Number Of Wires	4
Amperage Rating	30 Amps
Voltage Rating	600 V

Classifications

Brand Name	Russellstoll
Standard	UL e57324 UL e57324

ETIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	30 A
Number of poles	3