



Representative Image

Catalog No. DBRF3504030K0

Description: 30A,ILK,4P5W,MG,504,0K0,3PY480,FC

UPC No 708917133865

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

Flap Cap Interlocking Circuit Breaker Receptacle, Amperage 30A, Voltage 3 Phase Y 277/480V, 4 Poles 5 Wire, Breaker Trip Rating 30A, with 2 Control Contacts

Descriptors

Category	Electrical sleeves
----------	--------------------

Specifications

Number Of Poles	4
Number Of Wires	5
Amperage Rating	30 Amps
Voltage Rating	277/480 V

Classifications

Brand Name	Russellstoll
Standard	UL e57324 UL e57324

ETIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	30 A
Number of poles	4