



Representative Image

Catalog No. DBRF4414400K0

Description: 400A,ILK,3P4W,MG,414,400T,3P600V,FC

UPC No 708917303107

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Interlocked Flap Cap Receptacle with Circuit Breaker and Control Contacts, 400 Amp, 3 Pole 4 Wire, 30 600V, 60Hz

Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	For use with watertight plugs and inlets where portable equipment is on stand by and plugs are not in use.

Specifications

Number Of Poles	3
Number Of Wires	4
Amperage Rating	400 Amps
Voltage Rating	600 V
Material	Cast Aluminum

Classifications

Brand Name	Russellstoll
------------	--------------

ETIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	400 A
Number of poles	3