



Representative Image

## Catalog No. DBRF4504400K0

**Description: 400A,ILK,4P5W,MG,504,0K0,3PY480,FC**

**UPC No 708917269830**

**Home > Connectivity & Grounding > Russellstoll > Electrical sleeves**

MaxGard Interlocked Receptacle with Circuit Breaker and Control Contacts, 400 Amp, 4 Pole 5 Wire, 30Y 277/480V, 60Hz

### Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	For use with watertight plugs and inlets where portable equipment is on stand by and plugs are not in use.

### Specifications

Number Of Poles	4
Number Of Wires	5
Amperage Rating	400 Amps
Material	Cast Aluminum

### Classifications

Brand Name	Russellstoll
------------	--------------

### FTIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	400 A
Number of poles	4

by ABB