



Representative Image

Catalog No. DBRF610406000
Description: 60A,ILK,2P3W,MG,104,277V,FC
UPC No 708917268178
Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

Maxgard Interlocked Receptacle with Circuit Breaker, 60Amp, 2 Pole 3 Wire, 277V, 60Hz

Descriptors

Category	Electrical sleeves
----------	--------------------

Specifications

Number Of Poles	2
Number Of Wires	3
Amperage Rating	60 Amps
Voltage Rating	277 V

Classifications

Brand Name	Russellstoll
Standard	UL e57324 UL e57324

ETIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	60 A
Number of poles	2