



Representative Image

## Catalog No. DBRF640706000

**Description:** 60A,ILK,3P4W,MG,407,3P250V,FC

**UPC No** 708917204466

**Home > Connectivity & Grounding > Russellstoll > Electrical sleeves**

MaxGard Interlocked Receptacle with Circuit Breaker, 60 Amp, 3 Pole 4 Wire, 30 250V, 60Hz

### Descriptors

|                  |                                                                                                                                                                  |
|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Category         | Electrical sleeves                                                                                                                                               |
| Special Features | Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight"). |
| Application      | For use with watertight plugs and inlets where portable equipment is on stand by and plugs are not in use.                                                       |

### Specifications

|                 |               |
|-----------------|---------------|
| Number Of Poles | 3             |
| Number Of Wires | 4             |
| Amperage Rating | 60 Amps       |
| Voltage Rating  | 250 V         |
| Material        | Cast Aluminum |

### Classifications

|            |              |
|------------|--------------|
| Brand Name | Russellstoll |
|------------|--------------|

### ETIM Classification

|                 |                                              |
|-----------------|----------------------------------------------|
| ETIM            | EC001322 Round socket/plug for high currents |
| Amperage        | 60 A                                         |
| Number of poles | 3                                            |