



Representative Image

Catalog No. DBRS110410000

Description: 100A,ILK,2P3W,MG,104,277V,SC

UPC No 708917139041

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Interlocked Receptacle with Circuit Breaker, 100 Amp, 2 Pole 3 Wire, 277V, 60Hz

Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	For use with watertight plugs and inlets where portable equipment is on stand by and plugs are not in use.

Specifications

Number Of Poles	2
Number Of Wires	3
Amperage Rating	100 Amps
Voltage Rating	277 V
Material	Cast Aluminum

Classifications

Brand Name	Russellstoll
------------	--------------

ETIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	100 A
Number of poles	2