



Representative Image

Catalog No. DBRS340401500

Description: 30A,ILK,3P4W,MG,404,T15,3P480V,SC

UPC No 708917154310

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Interlocked Receptacle with Circuit Breaker with Screw Cap, 30 Amp, 3 Pole 4 Wire, 3 Phase 480V, 60Hz, Breaker Trip Rating 15 Amp

Descriptors

Category	Electrical sleeves
----------	--------------------

Specifications

Number Of Poles	3
Number Of Wires	4
Amperage Rating	30 Amps
Voltage Rating	480 V

Classifications

Brand Name	Russellstoll
------------	--------------

ETIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	30 A
Number of poles	3