



Representative Image

Catalog No. DBRS3414030KZ

Description: 30A,ILK,3P4W,MG,414,3P600V,CC,SHUNT

UPC No 708917305187

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Interlocked Receptacle with Circuit Breaker, Control Contacts and Shunt Trip Breaker, 30 Amp, 3 Pole 4 Wire, 30 600V, 60Hz

Descriptors

| | |
|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Category | Electrical sleeves |
| Special Features | Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight"). |
| Application | For use with watertight plugs and inlets where portable equipment is on stand by and plugs are not in use. |

Specifications

| | |
|-----------------|---------------|
| Number Of Poles | 3 |
| Number Of Wires | 4 |
| Amperage Rating | 30 Amps |
| Voltage Rating | 600 V |
| Material | Cast Aluminum |

Classifications

| | |
|------------|--------------|
| Brand Name | Russellstoll |
|------------|--------------|

ETIM Classification

| | |
|-----------------|----------------------------------------------|
| ETIM | EC001322 Round socket/plug for high currents |
| Amperage | 30 A |
| Number of poles | 3 |

by ABB