



Representative Image

## Catalog No. DBRS350403000

**Description:** 30A,ILK,4P5W,MG,504,3PY277/480,SC

**UPC No** 708917306641

**Home > Connectivity & Grounding > Russellstoll > Electrical receptacles**

MaxGard Interlocked Receptacle with Circuit Breaker with Screw Cap, 30 Amp, 4 Pole 5 Wire, 3 Phase Y 277/480V, 60Hz, Breaker Trip Rating 30 Amp

### Descriptors

|                  |                                                                                                                                                                  |
|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Category         | Electrical receptacles                                                                                                                                           |
| Special Features | Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight"). |
| Application      | For use with watertight plugs and inlets where portable equipment is on stand by and plugs are not in use.                                                       |

### Specifications

|          |               |
|----------|---------------|
| Material | Cast Aluminum |
|----------|---------------|

### Classifications

|            |              |
|------------|--------------|
| Brand Name | Russellstoll |
|------------|--------------|

### FTIM Classification

|                 |                                              |
|-----------------|----------------------------------------------|
| ETIM            | EC001322 Round socket/plug for high currents |
| Amperage        | 30 A                                         |
| Number of poles | 4                                            |