



Representative Image

## Catalog No. DBRS441440000

**Description: 400A,ILK W/CB,3P4W,MG,414,3P600V,SC**

**UPC No 708917312567**

**Home > Connectivity & Grounding > Russellstoll > Electrical sleeves**

MaxGard Interlocked Receptacle with Circuit Breaker with Screw Cap, 400 Amp, 3 Pole 4 Wire, 3 Phase 600V, 60Hz, Breaker Trip Rating 400 Amp

### Descriptors

|                  |  |
|------------------|--|
| Category         | Electrical sleeves   |
| Special Features | Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight"). |
| Application      | For use with watertight plugs and inlets where portable equipment is on stand by and plugs are not in use.   |

### Specifications

|                 |               |
|-----------------|---------------|
| Number Of Poles | 3             |
| Number Of Wires | 4             |
| Amperage Rating | 400 Amps      |
| Voltage Rating  | 600 V         |
| Material        | Cast Aluminum |

### Classifications

|            |              |
|------------|--------------|
| Brand Name | Russellstoll |
|------------|--------------|

### ETIM Classification

|                 |  |
|-----------------|--|
| ETIM            | EC001322 Round socket/plug for high currents |
| Amperage        | 400 A  |
| Number of poles | 3  |

by ABB