



Representative Image

Catalog No. DBRS450440000

Description: 400A,ILK,4P5W,MG,504,3PY480V,SC

UPC No 708917272489

Home > Connectivity & Grounding > Russellstoll > Electrical receptacles

MaxGard Interlocked Receptacle with Circuit Breaker with Screw Cap, 400 Amp, 4 Pole 5 Wire, 3 Phase Y 277/480V, 60Hz, Breaker Trip Rating 400 Amp

Descriptors

| | |
|------------------|--|
| Category | Electrical receptacles |
| Special Features | Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight"). |
| Application | For use with watertight plugs and inlets where portable equipment is on stand by and plugs are not in use. |

Specifications

| | |
|-----------------|---------------|
| Number Of Poles | 4 |
| Number Of Wires | 5 |
| Amperage Rating | 400 Amps |
| Voltage Rating | 277/480 V |
| Material | Cast Aluminum |

Classifications

| | |
|------------|--------------|
| Brand Name | Russellstoll |
|------------|--------------|

ETIM Classification

| | |
|-----------------|--|
| ETIM | EC001322 Round socket/plug for high currents |
| Amperage | 400 A |
| Number of poles | 4 |

