



Representative Image

Catalog No. DF1504FRA00

Description: 100A,REC,4P5W,MG,504,A00,3PY277

UPC No 708917132981

Home > Connectivity & Grounding > Russellstoll > Electrical receptacles

MaxGard Female Receptacle with Angle Adapter, 100 Amp, 4 Pole 5 Wire, 30Y 277/480V, 60Hz

Descriptors

|                  |                                                                                                                                                                  |
|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Category         | Electrical receptacles                                                                                                                                           |
| Special Features | Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight"). |
| Application      | Convention centers and areanas                                                                                                                                   |

Specifications

|          |               |
|----------|---------------|
| Material | Cast Aluminum |
|----------|---------------|

Classifications

|            |              |
|------------|--------------|
| Brand Name | Russellstoll |
|------------|--------------|

|                   |                                              |
|-------------------|----------------------------------------------|
| ETIM              | EC001322 Round socket/plug for high currents |
| Amperage          | 100 A                                        |
| Construction type | Wall socket                                  |
| Number of poles   | 4                                            |