



Representative Image

Catalog No. DF1507FRAB0

Description: 100A,REC,4P5W,MG,3PY 125/250V,FC

UPC No 708917312123

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Female Flap Cap Receptacle with Angle Adapter and Junction Box, 100 Amp, 4 Pole 5 Wire, 30Y 125/250V, 60Hz

Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	Convention centers and areanas

Specifications

Number Of Poles	4
Number Of Wires	5
Amperage Rating	100 Amps
Voltage Rating	250 V
Material	Cast Aluminum

Classifications

Brand Name	Russellstoll
------------	--------------

ETIM	EC001322 Round socket/plug for high currents
Amperage	100 A
Construction type	Wall socket
Number of poles	4