

## Catalog No. DS2504MP000/DF2032



Representative Image

**Description:** 200A PLG 4P5W MG 3PY277V 1.875INBSG

**UPC No** 708917266310

**Home > Connectivity & Grounding > Russellstoll > Electrical sleeves**

MaxGard Male Plug, 200 Amp, 4 Pole 5 Wire, 3 Phase Y 277/480V, 60Hz, with 1.875 Inch Bushing

### Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	Electrical hook-up of mobile medical imaging (MMI) trailers.

### Specifications

Number Of Poles	4
Number Of Wires	5
Amperage Rating	200 Amps
Voltage Rating	277 V
Material	Cast Aluminum

### Classifications

Brand Name	Russellstoll
------------	--------------

ETIM	EC001322 Round socket/plug for high currents
Amperage	200 A
Construction type	Plug
Number of poles	4

by ABB