



Representative Image

Catalog No. DF2207FRAB0**Description: 200A,REC,2P3W,MG,207,AB0,250****UPC No 708917134121****Home > Connectivity & Grounding > Russellstoll > Electrical receptacles**

MaxGard Female Receptacle with Angle Adapter and Junction Box, 200 Amp, 2 Pole 3 Wire, 250V, 60Hz

Descriptors

| | |
|------------------|--|
| Category | Electrical receptacles |
| Special Features | Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight"). |
| Application | Electrical hook-up of mobile medical imaging (MMI) trailers. |

Specifications

| | |
|----------|---------------|
| Material | Cast Aluminum |
|----------|---------------|

Classifications

| | |
|------------|--------------|
| Brand Name | Russellstoll |
|------------|--------------|

| | |
|-------------------|--|
| ETIM | EC001322 Round socket/plug for high currents |
| Amperage | 200 A |
| Construction type | Wall socket |
| Number of poles | 2 |

by ABB