



Representative Image

Catalog No. DF2404FRA0K

Description: 200A,REC,3P4W,MG,404,3P480V,CC

UPC No 708917306016

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Female Receptacle with Angle Adapter and Control Contacts, 200 Amp, 3 Pole 4 Wire, 30 480V, 60Hz

Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	Electrical hook-up of mobile medical imaging (MMI) trailers.

Specifications

Number Of Poles	3
Number Of Wires	4
Amperage Rating	200 Amps
Voltage Rating	480 V
Material	Cast Aluminum

Classifications

Brand Name	Russellstoll
------------	--------------

ETIM	EC001322 Round socket/plug for high currents
Amperage	200 A
Construction type	Wall socket
Number of poles	3